

The RadEye SX is a modern and compact multi-purpose meter that fits to most any external scintillation detector

## RadEye SX

Survey Meter for external scintillation probes



### Key Features

- The RadEye SX can operate with dual phosphor  $\alpha$  /  $\beta$ , NaI(Tl) and plastic probes
- Up to 16 different probe configurations are selectable in a submenu
- Easy to replace probes in-the-field, with a simple button-push
- Weighs only 160 g (5.6 oz) with rubber protection, without cable, 110 x 67 x 62 mm (4.3" x 2.6" x 2.4")
- Traditional probes can be used for one and two hand operation
- Versatile operation modes

The RadEye SX is a modern compact multi-purpose survey meter for external scintillator counter tubes. General count rate and surface contamination measurements can be performed as well as dose rate measurements.

As part of the growing RadEye product family of high-end stand-alone meters, the RadEye SX is designed to exceed the most demanding user expectations.

Due to the clear and large display all essential functions and software parameters can be easily accessed. The display and the alarm-LED can be seen while the instrument is worn in the transparent case.

All settings and the data analysis can be done by an optional Windows™-

based PC-software and a reader device. The last 1500 mean and maximum values of the count rate or dose rate are recorded internally and can be read out via a serial interface. Additionally the RadEye SX logs the last 250 alarms, error messages and changes of the configuration.

Operation modes:

- Scaler / Timer with preset count and preset time for sample measurements
- Continuous ratemeter mode for frisker operation
- Simultaneous  $\alpha$  /  $\beta$  and gross / ROI operation (distinct audible indication for each measuring channel)



RadEye BTcom cover for Bluetooth® communication

## RadEye SX Specifications

|                         |  |
|-------------------------|--|
| Measured quantities     | Count rate (cps, cpm), surface contamination (Bq, dps, dpm, Bq/cm <sup>2</sup> ), dose rate (R/h, Sv/h, rem/h).  |
| Background subtraction  | In count rate and contamination mode.  |
| Measuring range         | Default: 100,000 cps - extendable by individual probe calibration.   |
| Probe cables            | RG 58, max. 1.5 m (59") – MHV connector.   |
| High voltage range      | 100 V...1400 V with output impedance 2 MΩ.   |
| Probe library           | 16 different detectors with corresponding high voltage, calibration factor, dead time correction, overload threshold, detector area and timeout for detector failure.  |
| Alarm threshold         | Two alarm thresholds for count rate, activity, dose and dose rate each.  |
| Audible alarm intensity | 80 dB at a distance of 30 cm (11.8").  |
| Working temperature     | -20°C ... + 50°C (-4°F ... 122°F).   |
| Relative humidity       | 10 ... 90 % at 35°C (95°F) not condensing.   |
| Operating voltage       | 1,8 ... 4 V, battery low voltage starting from 2.3 V.  |
| Scaler/Timer            | Preset count, preset time.   |
| EMC                     | Disturbance emission: EN 61000-6-3, Immunity: EN 61000-6-2.  |
| Size                    | 110 mm x 67 mm x 62 mm (4.3" x 2.6" x 2.4"), with rubber protection, without cable.  |
| Weight                  | Around 160 g (5.6 oz) including AAA cells and protection sleeve.   |
| Internal memory         | The last 1500 measured values are saved and can be read out via PC program. Max and mean value of count rate and dose rate. The time interval is factory preset to 120 s by default. As well scaler measurements and momentaneous readings can be stored manually. Logbook with 250 entries for changes of configuration, occurring alarms and errors. |
| Averaging filters       | Ratemeter filter type: Advanced Digital Filter (ADF), Digital RC-Filter with time constant, 1s...180 s, depending on count rate and count rate change.   |
| Battery life time       | Depends on external detector (required high voltage and dynode chain impedance), > 500 h for instrument alone.   |

## RadEye SX Accessories

|   |   |   |   |
|---|---|---|---|
| Transparent case with lanyard<br># 425067044                      |   | The RadEye BTcom cover with manual and RadEye.exe update installation file<br># 425067087 |   |
| RadEye SX adapter for DP6 probe<br># 425069360                    |  | Holder with vacuum cup and goose neck # 425522005   |  |
| Probe cables MHV to MHV and MHV to PET, various lengths available |  | Right-angle-plug converter<br># KT 162245107  |  |
| Battery lid # 425067034 for inductive chargers                    |  | Desktop holder and inductive charger # 425067083  |  |

© 2010 Thermo Fisher Scientific Inc. All rights reserved. Windows is a registered trademark of Microsoft Corporation in United States and other countries. Bluetooth is a trademark of Bluetooth SIG, Inc., Bellevue, Washington, U.S.A. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Results may vary under different operating conditions. Thermo Fisher Scientific makes no warranties, expressed or implied, in this product summary. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representatives for details. LIT100816\_DB\_RadEye SX-e-V1.1

### Europe, Africa, Middle East & Countries Not Listed

Frauenauracher Strasse 96 +49 (0) 9131 998-226  
D 91056 Erlangen, Germany +49 (0) 9131 998-172 fax  
customerservice.eid.erlangen@thermofisher.com

### China

7th Floor, Tower West, Yonghe Plaza +86 10 8419 3588  
No. 28 Andingem E. Street, Beijing, 100007 China +86 10 8419 3581 fax  
info.eid.china@thermofisher.com

### Singapore

11 Biopolis Way, Helios, Units #12-07/08 +65 6478 9728  
Singapore 138667 +65 6478 9505 fax  
info.eid.singapore@thermofisher.com

### United Kingdom

Bath Road, Beenham, +44 (0) 118 971 5042  
Reading RG7 5PR United Kingdom +44 (0) 118 971 2835 fax  
customerservice.eid.beenham@thermofisher.com

### USA, Canada, Mexico, Central & South America

27 Forge Parkway +1 (508) 553 1700  
Franklin, MA 02038 USA +1 (800) 274 4212 US toll-free  
info.eid@thermofisher.com +1 (508) 520 2815 fax

### India

Plot No. C -327, T.T.C. Industrial Area, Pawne +91-22-41578800  
Navi Mumbai 400 705, India +91-22-41578801 fax  
info.eid.india@thermofisher.com

[www.thermoscientific.com/rmp](http://www.thermoscientific.com/rmp)

**Thermo**  
SCIENTIFIC